

# SMART SEAL LINER

SAFR / SADT / SBFR

**SAFR** rings begin 4.95 inches from the center of the distal end.

**SBFR** rings begin 3 inches from the center of the distal end.

**SADT** rings for:

- Sizes 20-28 begin 3 inches from the center of the distal end.
- Sizes 32-38 begin 5 inches from the center of the distal end.



## DESCRIPTION

The ALPS™ Smart Seal Liner features raised bands that grip the socket wall to form a secure interface. The low modulus bands stretch against the socket wall, while the smooth inner wall conforms easily to the residual limb. The Smart Seal Liner has a new seamless knitted construction with a modern look and is available in locking and cushion suspension. The locking version features a new distal construction to control distal distraction.



HIGH DENSITY  
(HD) GEL



LOCKING

3.0 OR 6.0 MM  
UNIFORM THICKNESS



CUSHION

3.0 OR 6.0 MM  
UNIFORM THICKNESS

## TOP FEATURES



Seamless knitted  
fabric



Innovative single  
piece construction



Offered with or without  
distal attachment




#makinglivesbetter


MAKING LIVES BETTER

# CROSS SECTION DIAGRAM

## 3.0MM UNIFORM




## 6.0MM UNIFORM



## HOW TO SIZE

Measurements taken  
6cm from the distal end



MEASURED  
SIZE (CM)



SAFR - CUSHION  
3.0MM or 6MM UNIFORM



SADT - LOCKING  
3.0MM or 6MM UNIFORM

20-23 cm

SADT20 (3 or 6)

24-25 cm

SADT24 (3 or 6)

26-27 cm

SAFR26 (3 or 6)

SADT26 (3 or 6)

28-31 cm

SAFR28 (3 or 6)

SADT28 (3 or 6)

32-37 cm

SAFR32 (3 or 6)

SADT32 (3 or 6)

38-43 cm

SAFR38 (3 or 6)

SADT38 (3 or 6)

MEASURED  
SIZE (CM)



SBFR - CUSHION  
3.0MM or 6MM UNIFORM

20-23 cm

SBFR20 (3 or 6)

24-25 cm

SBFR24 (3 or 6)

26-27 cm

SBFR26 (3 or 6)

28-31 cm

SBFR28 (3 or 6)

## PRODUCTS OFTEN USED WITH SMART SEAL



VACUUM  
INTEGRATED  
PUMP (VIP)



## SKIN RELIEVER (ENCP)

Use the Skin Reliever (ENCP) with the Smart Seal to compensate for volume fluctuations with continued use of same socket.

MEASURED  
SIZE (CM)

ENCP  
TAPERED 3.0MM-1.5MM

10-19 cm

ENCP16 (3 or 6)

20-27 cm

ENCP20 (3 or 6)

28-37 cm

ENCP28 (3 or 6)



T: 727.528.8566 | 800.574.5426 | F: 727.528.8862

[www.easyliner.com](http://www.easyliner.com) | [info@easyliner.com](mailto:info@easyliner.com)

2895 42nd Avenue North St. Petersburg, Florida 33714

