



Double Ended Adapters

①



②



③



④



1201,1202,1203,1204

DOUBLE ENDED ADAPTER

With pyramid receivers on both ends, these titanium/stainless steel adapters provide excellent adjustability options when clearance is limited. They are available in 32mm, 45mm, 60mm and 75mm height.

Warranty: 2 year

- ① Double Ended Adapter with Pyramid, 32mm
- ② Double Ended Adapter with Pyramid, 45mm
- ③ Double Ended Adapter with Pyramid, 60mm
- ④ Double Ended Adapter with Pyramid, 75mm

P/N	Material	Height	Product Weight	Weight Limit
① 1201T	Titanium	32mm	88g	136kg / 300lbs
② 1202T	Titanium	45mm	99g	136kg / 300lbs
③ 1203T	Titanium	60mm	113g	136kg / 300lbs
④ 1204T	Titanium	75mm	126g	136kg / 300lbs
① 1201S	Stainless Steel	32mm	150g	125kg / 275lbs
② 1202S	Stainless Steel	45mm	166g	125kg / 275lbs
③ 1203S	Stainless Steel	60mm	192g	125kg / 275lbs
④ 1204S	Stainless Steel	75mm	210g	125kg / 275lbs

Torque Value	Torque (Nm)	Hex (mm)
M8 Set Screw	15 Nm	4mm wrench

1205

TUBE WITH PYRAMID RECEIVER

The tube adapter provides optimum strength and options for low clearance requirements.

Warranty: 2 year



P/N	Material	Height	Product Weight	Weight Limit
1205T	Titanium	100mm	128g	136kg / 300lbs

Torque Value	Torque (Nm)	Hex (mm)
M8 Set Screw	15 Nm	4mm wrench



Tube Clamp Assembly



1211

TUBE CLAMP ASSEMBLY

① Titanium Tube Clamp Assembly

The titanium fixed adapter with 30mm aluminum tube has a permanent adapter at one end. It can be cut to length. The titanium adapter is forged and machined while the aluminum tube is extruded and shot peened for an optimum fatigue strength. This combination creates high quality, durable and strong component.

Warranty: 2 year

② Stainless Steel Tube Clamp Assembly

The stainless fixed adapter with 30mm aluminum tube has a permanent adapter at one end. It can be cut to length. The stainless steel adapter is made of high strength stainless steel alloy while the aluminum tube is extruded and shot peened for an optimum fatigue strength. This combination creates high quality, durable and strong component.

Warranty: 2 year

③ Aluminum Tube Clamp Assembly

The aluminum fixed adapter with 30mm aluminum tube has a permanent adapter at one end. It can be cut to length. The aluminum adapter is forged and machined while the aluminum tube is extruded and shot peened for an optimum fatigue strength. This combination creates high quality, durable and strong component.

Warranty: 2 year

④ Molded Stainless Steel Tube Clamp Assembly

The molded stainless steel fixed adapter with 30mm aluminum tube comes in two length 200mm and 400mm.

Warranty: 1 year

⑤ Aluminum Tube Clamp Assembly - One Piece

The aluminum fixed adapter with 30mm aluminum tube has a permanent adapter at one end. It can be cut to length. This one piece tube clamp assembly design makes this adapter great for aligning a prosthesis where space is limited. The aluminum adapter and tube combination is 3D forged and machined for optimum fatigue strength. This combination creates high quality and durable product while maintaining the light weight.

Warranty: 2 year

P/N	Material	Product Weight	Weight Limit
① 1211T	Titanium	306g	136kg / 300lbs
② 1211S	Stainless Steel	344g	114kg / 250lbs
③ 1211A	Aluminum	307g	114kg / 250lbs
④ 1211MS-200 1211MS-400	Molded SS Molded SS	201g 320g	90kg / 198lbs 90kg / 198lbs
⑥ 1211A-OP	Aluminum	280g	114kg / 250lbs

Torque Value	Torque (Nm)	Hex (mm)
M8 Set Screw	15 Nm	4mm wrench
M8 Set Screw (1211A/1211A-OP)	10 Nm	4mm wrench

MODULAR COMPONENTS

Tube Clamp Assembly



1241

TUBE CLAMP ASSEMBLY

Titanium Low Profile Tube Clamp Assembly

The low profile titanium fixed adapter with 30mm aluminum tube has a permanent adapter at one end. It can be cut to length. The titanium adapter is forged and machined while the aluminum tube with 223mm is extruded and shot peened for an optimum fatigue strength. This combination creates high quality, durable and strong component.

Warranty: 2 year

P/N	Material	Product Weight	Weight Limit
1241T	Titanium	232g	136kg / 300lbs

Torque Value	Torque (Nm)	Hex (mm)
M8 Set Screw	15 Nm	4mm wrench