


Socket Comfort – Application Aids



ContexGel.sleeve

ContexGel knee sleeve, 3 mm uniform



satined knee area of the inner surface



Designated use

- ContexGel-Knee Sleeves are suitable for below-knee amputees as knee holding support or as sealing cap for vacuum-socket technology (VST)
- additional guidance for the knee and stabilisation for short prostheses
- smaller sizes are used as holding supports in arm prosthetics

Characteristics

- thermoplastic mouldable at 60 °C (140 °F)
- satined knee area prevents tension sensations in the knee joint area
- for optimal hold in the distal and proximal area
- especially soft functional textile cover for easily rolling the liner up or down
- functional textile cover minimises longitudinal expansion
- excellent circular expansion adjusts to the socket- and stump-anatomy
- product recommendation additionally for vacuum-socket technology (VST)

Material

- wall thickness: 3 mm, conical shape
- soft ContexGel with medical white oil, antibacterially fitted
- approx. 25 – 30 Shore 00
- abrasion-proof textile cover made of polyamide/elastane
- colour: anthracite 30L1 / sand 30L5

Warranty

- 3 months

Colour: Anthracite

Size	Distal	Proximal	Length	Item-No.
S	15 – 23 cm	23 – 35 cm	37 cm	30L1/S
M	21 – 31 cm	29 – 44 cm	37 cm	30L1/M
L	28 – 43 cm	36 – 52 cm	38,5 cm	30L1/L
XL	34 – 48 cm	42 – 58 cm	38,5 cm	30L1/XL
XXL	38 – 52 cm	43 – 64 cm	38,5 cm	30L1/XXL

Colour: Sand

Size	Distal	Proximal	Length	Item-No.
S	15 – 23 cm	23 – 35 cm	37 cm	30L5/S
M	21 – 31 cm	29 – 44 cm	37 cm	30L5/M
L	28 – 43 cm	36 – 52 cm	38,5 cm	30L5/L
XL	34 – 48 cm	42 – 58 cm	38,5 cm	30L5/XL
XXL	38 – 52 cm	43 – 64 cm	38,5 cm	30L5/XXL



Sizing: ContexGel Knee Sleeves are available in 6 sizes. If possible, please position the sleeve with its middle at the MTP. Also taking measurements for the thigh circumference should start at this point 15 cm towards proximal. This will determine the optimal size of the knee sleeve for the patient.