

30-40mmHg AK 4-WAY STRETCH SHRINKER

WHITE POLYESTER/ LYCRA®	BLACK X-STATIC® POLYESTER/ X-STATIC®/LYCRA®	SIZE	FITS DISTAL LENGTH	LENGTH
2H-0HA1-08	2H-0HA0-08	I	8"; 20cm	Short
2H-0HA1-10	2H-0HA0-10	I	10"; 25cm	Medium
2H-0HA1-12	2H-XHA0-12	I	12"; 30.5cm	Long
2H-0HA1-14	2H-XHA1-14	I	14"; 35cm	X-Long
2H-0HA2-08	2H-XHA1-08	II	8"; 20cm	Short
2H-0HA2-10	2H-XHA1-10	II	10"; 25cm	Medium
2H-0HA2-12	2H-XHA2-12	II	12"; 30.5cm	Long
2H-0HA2-14	2H-XHA2-14	II	14"; 35cm	X-Long
2H-0HA3-08	2H-XHA2-08	III	8"; 20cm	Short
2H-0HA3-10	2H-XHA3-10	III	10"; 25cm	Medium
2H-0HA3-12	2H-XHA3-12	III	12"; 30.5cm	Long
2H-0HA3-14	2H-XHA3-14	III	14"; 35cm	X-Long
2H-0HA4-08	2H-XHA4-08	IV	8"; 20cm	Short
2H-0HA4-10	2H-XHA4-10	IV	10"; 25cm	Medium
2H-0HA4-12	2H-XHA4-12	IV	12"; 30.5cm	Long
2H-0HA4-14	2H-XHA5-14	IV	14"; 35cm	X-Long
2H-0HA5-08	2H-XHA5-08	V	8"; 20cm	Short
2H-0HA5-10	2H-XHA5-10	V	10"; 25cm	Medium
2H-0HA5-12	2H-XHA6-12	V	12"; 30.5cm	Long
2H-0HA5-14	2H-XHA6-14	V	14"; 35cm	X-Long
2H-0HA6-08	2H-XHA6-08	VI	8"; 20cm	Short
2H-0HA6-10	2H-XHA6-10	VI	10"; 25cm	Medium
2H-0HA6-12	2H-XHA6-12	VI	12"; 30.5cm	Long
2H-0HA6-14	2H-XHA6-14	VI	14"; 35cm	X-Long

30-40mmHg AK 4-WAY STRETCH SHRINKER

with Hip Attachment

WHITE POLYESTER/ LYCRA®	BLACK X-STATIC® POLYESTER/ X-STATIC®/LYCRA®	SIZE	FITS DISTAL LENGTH	LENGTH
2W-0HA1-08	2W-0HA1-08	I	8"; 20cm	Short
2W-0HA1-10	2W-0HA1-10	I	10"; 25cm	Medium
2W-0HA1-12	2W-XHA1-12	I	12"; 30.5cm	Long
2W-0HA1-14	2W-XHA1-14	I	14"; 35cm	X-Long
2W-0HA2-08	2W-XHA2-08	II	8"; 20cm	Short
2W-0HA2-10	2W-XHA2-10	II	10"; 25cm	Medium
2W-0HA2-12	2W-XHA2-12	II	12"; 30.5cm	Long
2W-0HA2-14	2W-XHA2-14	II	14"; 35cm	X-Long
2W-0HA3-08	2W-XHA3-08	III	8"; 20cm	Short
2W-0HA3-10	2W-XHA3-10	III	10"; 25cm	Medium
2W-0HA3-12	2W-XHA3-12	III	12"; 30.5cm	Long
2W-0HA3-14	2W-XHA3-14	III	14"; 35cm	X-Long
2W-0HA4-08	2W-XHA4-08	IV	8"; 20cm	Short
2W-0HA4-10	2W-XHA4-10	IV	10"; 25cm	Medium
2W-0HA4-12	2W-XHA4-12	IV	12"; 30.5cm	Long
2W-0HA4-14	2W-XHA4-14	IV	14"; 35cm	X-Long
2W-0HA5-08	2W-XHA5-08	V	8"; 20cm	Short
2W-0HA5-10	2W-XHA5-10	V	10"; 25cm	Medium
2W-0HA5-12	2W-XHA5-12	V	12"; 30.5cm	Long
2W-0HA5-14	2W-XHA5-14	V	14"; 35cm	X-Long
2W-0HA6-08	2W-XHA6-08	VI	8"; 20cm	Short
2W-0HA6-10	2W-XHA6-10	VI	10"; 25cm	Medium
2W-0HA6-12	2W-XHA6-12	VI	12"; 30.5cm	Long
2W-0HA6-14	2W-XHA6-14	VI	14"; 35cm	X-Long



SOLUTIONS THAT FIT™



4-WAY
STRETCH
SHRINKER
WITH ROUNDED TOE


The 4-Way Stretch Shrinker features stretchy core-spun yarns providing multidirectional stretch for a shrinker that is softer, more comfortable to wear, and easier to don.

Available in Medium (20–30mmHg) and Heavy (30–40mmHg) compression, Transtibial and Transfemoral sizes.

- ▶ Multidirectional stretch provides improved fit qualities and comfort
- ▶ Softer, more comfortable and easier to don
- ▶ Dot silicone suspension band
- ▶ Moisture transport properties
- ▶ AK version also available with waist belt
- ▶ Black version includes X-STATIC® Silver Fiber to help prevent odor
- ▶ High quality, exceptional bottom line




ORDERING GUIDELINES



For more information contact Knit-Rite at
800-821-3094 or customerservice@knitrite.com.






BK SHRINKER

20–30mmHg
30–40mmHg

Measure the circumference of areas F, E, and C to find the correct size.
Measure from the end of the limb up to the F area to find the correct length.

		F	E	C
LENGTHS	SIZE	CIRCUMFERENCES		
SHORT 12" (30cm)	0	14" – 15.75" (35.5 – 40cm)	10.75" – 11.75" (27 – 30cm)	10" – 11" (25.5 – 28cm)
MEDIUM 15" (38cm)	1	15.75" – 16.75" (40 – 42.5cm)	11.75" – 12.75" (30 – 32cm)	11" – 12" (28 – 30cm)
LONG 18" (46cm)	2	16.75" – 17.75" (42.5 – 45cm)	12.75" – 14" (32 – 35.5cm)	12" – 13" (30 – 33cm)
	3	17.75" – 19" (45 – 48 cm)	14" – 15" (35.5 – 38cm)	13" – 14.5" (33 – 37cm)
	4	19" – 20.25" (48 – 51.5cm)	15" – 16.25" (38 – 41cm)	14.5" – 15.5" (37 – 39cm)
	5	20.25" – 21.25" (51.5 – 54cm)	16.25" – 17.5" (41 – 44.5cm)	15.5" – 16.75" (39 – 42.5cm)
	6	21.25" – 22.75" (54 – 58cm)	17.5" – 18.5" (44.5 – 47cm)	16.75" – 17.75" (42.5 – 45cm)



AK SHRINKER

20–30mmHg
30–40mmHg

Measure the circumference of areas G, F, and E to find the correct size.
Measure from the end of the limb up to the F area to find the correct length.

		G	F	E
LENGTHS	SIZE	CIRCUMFERENCES		
SHORT 8" (20cm)	0	15.5" – 16.75" (39 – 42.5cm)	14.75" – 15.75" (37.5 – 40cm)	10.75" – 11.75" (27 – 30cm)
MEDIUM 10" (25cm)	1	16.75" – 18" (42.5 – 46cm)	15.75" – 16.75" (40 – 42.5cm)	11.75" – 12.75" (30 – 32cm)
LONG 12" (30cm)	2	18" – 19.75" (46 – 50cm)	16.75" – 17.75" (42.5 – 45cm)	12.75" – 14" (32 – 35.5cm)
X-LONG* 14" (35cm)	3	19.75" – 21.25" (50 – 54 cm)	17.75" – 19" (45 – 48cm)	14" – 15" (35.5 – 38cm)
	4	21.25" – 23" (54 – 58.5cm)	19" – 20.25" (48 – 51.5cm)	15" – 16.5" (38 – 42cm)
	5	23" – 24.5" (58.5 – 62cm)	20.25" – 21.25" (51.5 – 54cm)	16.5" – 17.5" (42 – 44.5cm)
	6	24.25" – 26.25" (62 – 66.5cm)	21.25" – 22.75" (54 – 58cm)	17.5" – 18.5" (44.5 – 47cm)

*Extra Long is not available in size 0.
A/K version with waist belt is not available in size 0. 30–40mmHg A/K is not available in size 0.

20–30mmHg BK 4-WAY STRETCH SHRINKER

WHITE POLYESTER/ LYCRA®	BLACK X-STATIC® POLYESTER/ X-STATIC®/LYCRA®	SIZE	FITS DISTAL LENGTH	LENGTH
2H-OMB0-12	2H-XMB0-12	0	12"; 30.5cm	Short
2H-OMB0-15	2H-XMB0-15	0	15"; 38.1cm	Medium
2H-OMB0-18	2H-XMB0-18	0	18"; 45.7cm	Long
2H-OMB1-12	2H-XMB1-12	I	12"; 30.5cm	Short
2H-OMB1-15	2H-XMB1-15	I	15"; 38.1cm	Medium
2H-OMB1-18	2H-XMB1-18	I	18"; 45.7cm	Long
2H-OMB2-12	2H-XMB2-12	II	12"; 30.5cm	Short
2H-OMB2-15	2H-XMB2-15	II	15"; 38.1cm	Medium
2H-OMB2-18	2H-XMB2-18	II	18"; 45.7cm	Long
2H-OMB3-12	2H-XMB3-12	III	12"; 30.5cm	Short
2H-OMB3-15	2H-XMB3-15	III	15"; 38.1cm	Medium
2H-OMB3-18	2H-XMB3-18	III	18"; 45.7cm	Long
2H-OMB4-12	2H-XMB4-12	IV	12"; 30.5cm	Short
2H-OMB4-15	2H-XMB4-15	IV	15"; 38.1cm	Medium
2H-OMB4-18	2H-XMB4-18	IV	18"; 45.7cm	Long
2H-OMB5-12	2H-XMB5-12	V	12"; 30.5cm	Short
2H-OMB5-15	2H-XMB5-15	V	15"; 38.1cm	Medium
2H-OMB5-18	2H-XMB5-18	V	18"; 45.7cm	Long
2H-OMB6-12	2H-XMB6-12	VI	12"; 30.5cm	Short
2H-OMB6-15	2H-XMB6-15	VI	15"; 38.1cm	Medium
2H-OMB6-18	2H-XMB6-18	VI	18"; 45.7cm	Long

30–40mmHg BK 4-WAY STRETCH SHRINKER

WHITE POLYESTER/ LYCRA®	BLACK X-STATIC® POLYESTER/ X-STATIC®/LYCRA®	SIZE	FITS DISTAL LENGTH	LENGTH
2H-OHB0-12	2H-OHB0-12	0	12"; 30.5cm	Short
2H-OHB0-15	2H-OHB0-15	0	15"; 38.1cm	Medium
2H-OHB0-18	2H-XHB0-18	0	18"; 45.7cm	Long
2H-OHB1-12	2H-XHB1-12	I	12"; 30.5cm	Short
2H-OHB1-15	2H-XHB1-15	I	15"; 38.1cm	Medium
2H-OHB1-18	2H-XHB1-18	I	18"; 45.7cm	Long
2H-OHB2-12	2H-XHB2-12	II	12"; 30.5cm	Short
2H-OHB2-15	2H-XHB2-15	II	15"; 38.1cm	Medium
2H-OHB2-18	2H-XHB2-18	II	18"; 45.7cm	Long
2H-OHB3-12	2H-XHB3-12	III	12"; 30.5cm	Short
2H-OHB3-15	2H-XHB3-15	III	15"; 38.1cm	Medium
2H-OHB3-18	2H-XHB3-18	III	18"; 45.7cm	Long
2H-OHB4-12	2H-XHB4-12	IV	12"; 30.5cm	Short
2H-OHB4-15	2H-XHB4-15	IV	15"; 38.1cm	Medium
2H-OHB4-18	2H-XHB4-18	IV	18"; 45.7cm	Long
2H-OHB5-12	2H-XHB5-12	V	12"; 30.5cm	Short
2H-OHB5-15	2H-XHB5-15	V	15"; 38.1cm	Medium
2H-OHB5-18	2H-XHB5-18	V	18"; 45.7cm	Long
2H-OHB6-12	2H-XHB6-12	VI	12"; 30.5cm	Short
2H-OHB6-15	2H-XHB6-15	VI	15"; 38.1cm	Medium
2H-OHB6-18	2H-XHB6-18	VI	18"; 45.7cm	Long

20–30mmHg AK 4-WAY STRETCH SHRINKER

WHITE POLYESTER/ LYCRA®	BLACK X-STATIC® POLYESTER/ X-STATIC®/LYCRA®	SIZE	FITS DISTAL LENGTH	LENGTH
2H-OMA0-08	2H-OMA0-08	0	8"; 20cm	Short
2H-OMA0-10	2H-OMA0-10	0	10"; 25cm	Medium
2H-OMA0-12	2H-XMA0-12	0	12"; 30.5cm	Long
2H-OMA1-08	2H-XMA1-08	I	8"; 20cm	Short
2H-OMA1-10	2H-XMA1-10	I	10"; 25cm	Medium
2H-OMA1-12	2H-XMA1-12	I	12"; 30.5cm	Long
2H-OMA2-14	2H-XMA2-14	I	14"; 35cm	X-Long
2H-OMA2-08	2H-XMA2-08	II	8"; 20cm	Short
2H-OMA2-10	2H-XMA2-10	II	10"; 25cm	Medium
2H-OMA3-12	2H-XMA3-12	II	12"; 30.5cm	Long
2H-OMA3-14	2H-XMA3-14	II	14"; 35cm	X-Long
2H-OMA3-08	2H-XMA3-08	III	8"; 20cm	Short
2H-OMA4-10	2H-XMA4-10	III	10"; 25cm	Medium
2H-OMA4-12	2H-XMA4-12	III	12"; 30.5cm	Long
2H-OMA4-14	2H-XMA4-14	III	14"; 35cm	X-Long
2H-OMA5-08	2H-XMA5-08	IV	8"; 20cm	Short
2H-OMA5-10	2H-XMA5-10	IV	10"; 25cm	Medium
2H-OMA5-12	2H-XMA5-12	IV	12"; 30.5cm	Long
2H-OMA6-14	2H-XMA6-14	IV	14"; 35cm	X-Long
2H-OMA6-08	2H-XMA6-08	V	8"; 20cm	Short
2H-OMA6-10	2H-XMA6-10	V	10"; 25cm	Medium
2H-OMA6-12	2H-XMA6-12	V	12"; 30.5cm	Long
2H-OMA6-14	2H-XMA6-14	V	14"; 35cm	X-Long
2H-OMA6-08	2H-XMA6-08	VI	8"; 20cm	Short
2H-OMA6-10	2H-XMA6-10	VI	10"; 25cm	Medium
2H-OMA6-12	2H-XMA6-12	VI	12"; 30.5cm	Long
2H-OMA6-14	2H-XMA6-14	VI	14"; 35cm	X-Long

20–30mmHg AK 4-WAY STRETCH SHRINKER

with Hip Attachment

WHITE POLYESTER/ LYCRA®	BLACK X-STATIC® POLYESTER/ X-STATIC®/LYCRA®	SIZE	FITS DISTAL LENGTH	LENGTH
2W-OMA1-08	2W-OMA1-08	I	8"; 20cm	Short
2W-OMA1-10	2W-OMA1-10	I	10"; 25cm	Medium
2W-OMA1-12	2W-XMA1-12	I	12"; 30.5cm	Long
2W-OMA1-08	2W-XMA1-08	I	14"; 35cm	X-Long
2W-OMA2-10	2W-XMA2-10	II	8"; 20cm	Short
2W-OMA2-12	2W-XMA2-12	II	10"; 25cm	Medium
2W-OMA2-14	2W-XMA2-14	II	12"; 30.5cm	Long
2W-OMA2-08	2W-XMA2-08	II	14"; 35cm	X-Long
2W-OMA3-10	2W-XMA3-10	III	8"; 20cm	Short
2W-OMA3-12	2W-XMA3-12	III	10"; 25cm	Medium
2W-OMA3-14	2W-XMA3-14	III	12"; 30.5cm	Long
2W-OMA3-08	2W-XMA3-08	III	14"; 35cm	X-Long
2W-OMA4-10	2W-XMA4-10	IV	8"; 20cm	Short
2W-OMA4-12	2W-XMA4-12	IV	10"; 25cm	Medium
2W-OMA4-14	2W-XMA4-14	IV	12"; 30.5cm	Long
2W-OMA4-08	2W-XMA4-08	IV	14"; 35cm	X-Long
2W-OMA5-10	2W-XMA5-10	V	8"; 20cm	Short
2W-OMA5-12	2W-XMA5-12	V	10"; 25cm	Medium
2W-OMA5-14	2W-XMA5-14	V	12"; 30.5cm	Long
2W-OMA5-08	2W-XMA5-08	V	14"; 35cm	X-Long
2W-OMA6-10	2W-XMA6-10	VI	8"; 20cm	Short
2W-OMA6-12	2W-XMA6-12	VI	10"; 25cm	Medium
2W-OMA6-14	2W-XMA6-14	VI	12"; 30.5cm	Long
2W-OMA6-08	2W-XMA6-08	VI	14"; 35cm	X-Long