

UltraSeal Liner (High Ring) Sizing Chart

Ring: The high ring begins 7 inches from the center of the distal end.

How to Size: Measure the circumference of the residual limb at 6 cm above the distal end.

MEASURED SIZE (CM)	HIGH RING LOCKING 3.0MM UNIFORM	HIGH RING CUSHION 3.0MM UNIFORM
20-21 cm	USHSL20	USHSC20
22-23 cm	USHSL22	USHSC22
24-25 cm	USHSL24	USHSC24
26-27 cm	USHSL26	USHSC26
28-29 cm	USHSL28	USHSC28
30-31 cm	USHSL30	USHSC30
32-34 cm	USHSL32	USHSC32
35-37 cm	USHSL35	USHSC35
38-40 cm	USHSL38	USHSC38
41-43 cm	USHSL41	USHSC41
44-47 cm	USHSL44	USHSC44