

PARALEX

Combining the world's highest tech fibers...

**CARBON + NSP = Stiffness + Strength =
½ the weight = Thin laminations = Durability
= PARALEX**



Product Description	Product #
PARALEX Tube – 3" x 10 feet	4017-3.10
PARALEX Tube – 3" x 50 feet	4017-3.50
PARALEX Tube – 4" x 10 feet	4017-4.10
PARALEX Tube – 4" x 50 feet	4017-4.50
PARALEX Tube – 5" x 10 feet	4017-5.10
PARALEX Tube – 5" x 50 feet	4017-5.50
PARALEX Tube – 6" x 10 feet	4017-6.10
PARALEX Tube – 6" x 50 feet	4017-6.50
PARALEX Tube – 8" x 10 feet	4017-8.10
PARALEX Tube – 8" x 50 feet	4017-8.50
PARALEX Tube – 10" x 10 feet	4017-10.10
PARALEX Tube – 10" x 50 feet	4017-10.50




ST&G USA CORPORATION
2691 Saturn Street
Brea, CA 92821

TELEPHONE: (714) 524-0663
FAX: (714) 364-8113
E-MAIL: info@stngco.com



www.stngco.com



PARALEX

Combining the best of two fibers

PARALEX blends Carbon and **NSP** to create a new and dynamic hybrid material.

Cutting PARALEX Fiber:

- Before cutting PARALEX fiber, tape the edge of the fiber with masking tape then cut down the middle of the tape line.
- Use a scissor with a serrated edge.
- If you attempt to cut PARALEX fiber with a smooth bladed scissor, use very sharp scissors then fold the braid over on itself - (doubling up) greatly helps.

Lamination:

For the best edging results, the use of Perlon, nylons or 1/2oz Dacron felt is ideal as the first layer and the last layer.

- **For best results use 80:20 resin**

Grinding:

- Use high speed and low pressure.
- Only use sharp abrasives, dull abrasives will create friction and will "burn off" the resin and leave exposed fibers at your edge.

PARALEX Technical Data

Edging Techniques:

(The use of inner and outer finish layers is required. See example layups below.)

Finishing edge instructions: Finish as you would any composite by wet sanding using 220 grit and finish with 400 grit wet/dry sanding paper.

Example Layup TT:

- Typical TT
- 1 layer of 1/2oz felt or 2 layers of Perlon or nylon
- 1 layer of PARALEX
- 2 layers of Nyglass or equivalent.
- 1 layer of PARALEX
- 2 layers of sheer nylon or equivalent

Example Layup TF:

- Typical TF
- 1 layer of 1/2oz felt or 2 layers of Perlon or nylon
- 1 layer of PARALEX
- 2 layers of Nyglass or equivalent.
- 1 layer of PARALEX
- 2 layers of sheer nylon or equivalent

ST&G CORPORATION

2691 Saturn Street
Brea CA 92821, U.S.A
OFFICE: 714-524-0663
FAX: 714-364-8113

www.stngco.com

